

Garant
Clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 20/12mm

Order data

Order number	250019 20/12
GTIN	4045197650016
Item class	21T

Technical description

Shank size	20 mm
Insert size	12 mm
Shim	259031 2
Lever screw	259018 2
ISO code toolholder	PCLNR/L 2020K12
suitable indexable insert	CN.. 1204..
Functional width L ₄	25 mm
Head length L ₁	28 mm
Shim pins pack	259044 2
Shim punches pack	259047 2
Lever	259015 2
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2