

**Garant**

**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,  
Shank / insert size: 20/12mm**



### Order data

Order number	250018 20/12
GTIN	4045197649959
Item class	21T

### Technical description

Shim punches pack	259047 2
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Lever	259015 2
ISO code toolholder	PCLNR/L 2020K12
Head length L <sub>1</sub>	28 mm
Functional width L <sub>4</sub>	25 mm
Shim pins pack	259044 2
Shank size	20 mm
Shim	259031 2
Lever screw	259018 2
Overall length L	125 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2