

Garant

**Clamping toolholder PCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 25/12mm**



Order data

Order number	250018 25/12
GTIN	4045197649966
Item class	21T

Technical description

ISO code toolholder	PCLNR/L 2525M12
Functional width L ₄	32 mm
Shim	259031 2
Shim pins pack	259044 2
Shim punches pack	259047 2
Insert size	12 mm
Head length L ₁	33 mm
Lever screw	259018 2
suitable indexable insert	CN.. 1204..
Lever	259015 2
Shank size	25 mm
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2