

**Garant**
**Clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 32/12mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 250019 32/12  |
| GTIN         | 4045197654342 |
| Item class   | 21T           |

**Technical description**

|                                 |                 |
|---------------------------------|-----------------|
| Shank size                      | 32 mm           |
| Lever screw                     | 259018 2        |
| Functional width L <sub>4</sub> | 40 mm           |
| suitable indexable insert       | CN.. 1204..     |
| ISO code toolholder             | PCLNR/L 3232P12 |
| Shim pins pack                  | 259044 2        |
| Shim punches pack               | 259047 2        |
| Lever                           | 259015 2        |
| Shim                            | 259031 2        |
| Insert size                     | 12 mm           |
| Head length L <sub>1</sub>      | 30 mm           |
| Overall length L                | 170 mm          |
| Standard                        | Works standard  |
| Application type                | left-hand       |
| Through-coolant                 | no              |

|                        |                               |
|------------------------|-------------------------------|
| Setting angle $\kappa$ | 95 degrees                    |
| Application            | External longitudinal turning |
| Application            | External longitudinal turning |
| Type of product        | Boring bar                    |

---

## Accessories

|                                   |          |
|-----------------------------------|----------|
| Lever Type 2                      | 259015 2 |
| Lever screw Type 2                | 259018 2 |
| Shim Type 2                       | 259031 2 |
| Set of shim pins 10 pieces Type 2 | 259044 2 |
| Shim punches set 10 pieces Type 2 | 259047 2 |