

Garant
Clamping toolholder PCSNL 45°, for indexable inserts CN., left-hand, Shank / insert size: 20/12mm

Order data

Order number	250025 20/12
GTIN	4045197650153
Item class	21T

Technical description

Shim punches pack	259047 2
Shim pins pack	259044 2
Functional width L ₄	25 mm
Lever	259015 2
suitable indexable insert	CN.. 1204..
Head length L ₁	28 mm
ISO code toolholder	PCSNR/L 2020K12
Shim	259031 2
Insert size	12 mm
Lever screw	259018 2
Shank size	20 mm
Overall length L	125 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2