

**Garant**

**Steel boring bar A.. PCLNR 95°, for indexable inserts CN.., right-hand, Shank Ø / insert size: 40/16mm**


**Order data**

Order number	250036 40/16
GTIN	4045197654373
Item class	21T

**Description**
**Version:**

PCLNR 95° boring bars for indexable inserts CN..

**Technical description**

Insert size	16 mm
Centre offset $L_3$	27 mm
Lever screw	259018 11
Shim punches pack	259047 4
ISO code toolholder	A40T PCLNR/L16
Shim	259031 35
suitable indexable insert	CN.. 1606..
Shim pins pack	259044 6
Minimum pre-drill $\varnothing D_{\min}$	50 mm
Lever	259015 12
Overall length L	300 mm
Clamping height $L_2$	38.5 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	40 mm

Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

## Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15