

**Garant**
**Clamping toolholder PCBNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 25/12mm**

**Order data**

Order number	250021 25/12
GTIN	4045197650085
Item class	21T

**Technical description**

Functional width L <sub>4</sub>	32 mm
Lever	259015 2
suitable indexable insert	CN.. 1204..
ISO code toolholder	PCBNR/L 2525M12
Lever screw	259018 2
Head length L <sub>1</sub>	33 mm
Shim	259031 2
Insert size	12 mm
Shank size	25 mm
Shim pins pack	259044 2
Shim punches pack	259047 2
Overall length L	150 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2