

Garant

Steel boring bar A.. PCLNR 95°, for indexable inserts CN., right-hand, Shank Ø / insert size: 50/16mm


Order data

Order number	250036 50/16
GTIN	4045197654380
Item class	21T

Description
Version:

PCLNR 95° boring bars for indexable inserts CN..

Technical description

suitable indexable insert	CN.. 1606..
ISO code toolholder	A50U PCLNR/L16
Minimum pre-drill Ø D_{min}	63 mm
Centre offset L_3	35 mm
Insert size	16 mm
Shim punches pack	259047 4
Shim pins pack	259044 6
Shim	259031 35
Lever screw	259018 11
Lever	259015 12
Overall length L	350 mm
Clamping height L_2	48 mm
Setting angle κ	95 degrees
Shank Ø D_s	50 mm

Standard	DIN 8024
Application type	right-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15