

Garant
**Clamping toolholder PCKNR 75°, for indexable inserts CN., right-hand,
Shank / insert size: 20/12mm**

Order data

Order number	250022 20/12
GTIN	4045197650092
Item class	21T

Technical description

Lever	259015 2
Shim	259031 2
ISO code toolholder	PCKNR/L 2020K12
Head length L ₁	28 mm
suitable indexable insert	CN.. 1204..
Insert size	12 mm
Shim punches pack	259047 2
Lever screw	259018 2
Shim pins pack	259044 2
Functional width L ₄	25 mm
Shank size	20 mm
Overall length L	125 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2