

Garant

Steel boring bar A.. PCLNR 95°, for indexable inserts CN., right-hand, Shank Ø / insert size: 20/09mm


Order data

Order number	250036 20/09
GTIN	4045197650177
Item class	21T

Description
Version:

PCLNR 95° boring bars for indexable inserts CN..

Technical description

Lever	259015 11
Insert size	9 mm
suitable indexable insert	CN.. 09T3..
ISO code toolholder	A20Q PCLNR/L09
Lever screw	259018 9
Centre offset L_3	13 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Overall length L	180 mm
Clamping height L_2	18 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Lever Type 11	259015 11
Lever screw Type 10	259018 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2