

Garant
Clamping toolholder PCKNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 25/12mm

Order data

Order number	250023 25/12
GTIN	4045197650122
Item class	21T

Technical description

Head length L ₁	33 mm
ISO code toolholder	PCKNR/L 2525M12
Insert size	12 mm
Shim punches pack	259047 2
Shim pins pack	259044 2
Functional width L ₄	32 mm
Shank size	25 mm
Lever	259015 2
suitable indexable insert	CN.. 1204..
Lever screw	259018 2
Shim	259031 2
Overall length L	150 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 2	259015 2
Lever screw Type 2	259018 2
Shim Type 2	259031 2
Set of shim pins 10 pieces Type 2	259044 2
Shim punches set 10 pieces Type 2	259047 2