

Garant
Clamping toolholder PCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 32/16mm

Order data

Order number	250019 32/16
GTIN	4045197650030
Item class	21T

Technical description

Functional width L ₄	40 mm
Shim	259031 35
Insert size	16 mm
Head length L ₁	40 mm
Shank size	32 mm
Shim pins pack	259044 6
Lever	259015 12
suitable indexable insert	CN.. 1606..
ISO code toolholder	PCLNR/L 3232P16
Lever screw	259018 11
Shim punches pack	259047 4
Overall length L	170 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4