

Garant

Steel boring bar A.. PCLNL 95°, for indexable inserts CN., left-hand, Shank Ø / insert size: 50/16mm


Order data

Order number	250037 50/16
GTIN	4045197654427
Item class	21T

Technical description

Shim pins pack	259044 6
Lever	259015 12
Insert size	16 mm
Lever screw	259018 11
Shim	259031 35
Shim punches pack	259047 4
ISO code toolholder	A50U PCLNR/L16
Centre offset L_3	35 mm
Minimum pre-drill $\varnothing D_{\min}$	63 mm
suitable indexable insert	CN.. 1606..
Overall length L	350 mm
Clamping height L_2	48 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	50 mm
Standard	DIN 8024
Application type	left-hand

Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15