

Garant

Clamping toolholder SCLCR 95°, for indexable inserts CC., right-hand, Shank / insert size: 8/06mm



Order data

Order number	260006 8/06
GTIN	4045197651594
Item class	21T

Technical description

suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 22
Insert size	6 mm
Head length L ₁	9 mm
ISO code toolholder	SCLCR/L 0808D06
Functional width L ₄	10 mm
Shank size	8 mm
Overall length L	60 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 22

269028 22