

**Garant**
**Clamping toolholder SCLCR 95°, for indexable inserts CC., right-hand, Shank / insert size: 20/09mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 260006 20/09  |
| GTIN         | 4045197651631 |
| Item class   | 21T           |

**Technical description**

|                                 |                               |
|---------------------------------|-------------------------------|
| Shank size                      | 20 mm                         |
| Head length L <sub>1</sub>      | 17 mm                         |
| Shim screw                      | 269013 2                      |
| Shim                            | 269005 1                      |
| Functional width L <sub>4</sub> | 25 mm                         |
| suitable indexable insert       | CC.. 09T3..                   |
| ISO code toolholder             | SCLCR/L 2020K09               |
| Pack of insert screws           | 269028 2                      |
| Insert size                     | 9 mm                          |
| Overall length L                | 125 mm                        |
| Standard                        | Works standard                |
| Application type                | right-hand                    |
| Through-coolant                 | no                            |
| Setting angle κ                 | 95 degrees                    |
| Application                     | External longitudinal turning |

|                 |                               |
|-----------------|-------------------------------|
| Application     | External longitudinal turning |
| Type of product | Boring bar                    |

---

## Accessories

|                                                                                      |             |
|--------------------------------------------------------------------------------------|-------------|
| Shim Type 1                                                                          | 269005 1    |
| Shim screw Type 2                                                                    | 269013 2    |
| Set of insert screws Type 2                                                          | 269028 2    |
| Set of insert screws Type 22                                                         | 269028 22   |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500  |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15                            | 674248 TX15 |