

Garant

**HSS boring bar AH.. SCLCR 95°, for indexable inserts CC., right-hand, Shank
Ø / insert size: 0608/06mm**


Order data

Order number	260022 0608/06
GTIN	4045197651983
Item class	21T

Technical description

Head length L_1	25 mm
Centre offset L_3	4 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
ISO code toolholder	AH0608H SCLCR/L06
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Insert size	6 mm
Neck width L_4	6 mm
Overall length L	100 mm
Clamping height L_2	7 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8