

**Garant**

**HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 0410/03mm**


**Order data**

Order number	260023 0410/03
GTIN	4045197652089
Item class	21T

**Technical description**

Pack of insert screws	269028 13
Centre offset $L_3$	2.5 mm
suitable indexable insert	CC.. 0301..
ISO code toolholder	AH0410H SCLCR/L03
Head length $L_1$	24 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Neck width $L_4$	4 mm
Insert size	3 mm
Overall length $L$	100 mm
Clamping height $L_2$	9 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 13	269028 13
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6