

Garant

Carbide boring bar E.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 6/03mm



Order data

Order number	260016 6/03
GTIN	4045197651792
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	7 mm
Insert size	3 mm
Centre offset L ₃	3.5 mm
Pack of insert screws	269028 19
Head length L ₁	10 mm
suitable indexable insert	CC.. 0301..
ISO code toolholder	E06J SCLCR/L03
Overall length L	110 mm
Clamping height L ₂	5.8 mm
Setting angle κ	95 degrees
Shank Ø D _s	6 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 19	269028 19
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6