

Garant

HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 0610/03mm


Order data

Order number	260023 0610/03
GTIN	4045197652096
Item class	21T

Technical description

Head length L_1	24 mm
Pack of insert screws	269028 13
Neck width L_4	6 mm
suitable indexable insert	CC.. 0301..
Insert size	3 mm
ISO code toolholder	AH0610H SCLCR/L03
Centre offset L_3	2.5 mm
Minimum pre-drill $\varnothing D_{min}$	7 mm
Overall length L	100 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 13	269028 13
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6