

Garant
HSS boring bar AH.. SCLCR, for indexable inserts CC., right-hand

Order data

Order number	260024
GTIN	4045197652201
Item class	29W

Technical description

suitable indexable insert	CC.. 0602..
ISO code toolholder	AH0810J SCLCR/L06
ISO code toolholder	AH0608H SCLCR/L06
ISO code toolholder	AH1012K SCLCR/L06
ISO code toolholder	AH1216M SCLCR/L06
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	8 mm
Minimum pre-drill $\varnothing D_{min}$	12 mm
Minimum pre-drill $\varnothing D_{min}$	14 mm
Minimum pre-drill $\varnothing D_{min}$	18 mm
Clamping height L_2	7 mm
Clamping height L_2	9 mm
Clamping height L_2	11 mm
Clamping height L_2	15 mm

Centre offset L ₃	4 mm
Centre offset L ₃	6 mm
Centre offset L ₃	7 mm
Centre offset L ₃	9 mm
Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
Overall length L	150 mm
Neck width L ₄	6 mm
Neck width L ₄	8 mm
Neck width L ₄	10 mm
Neck width L ₄	12 mm
Overhang L ₁	50 mm
Overhang L ₁	38 mm
Overhang L ₁	32 mm
Overhang L ₁	25 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar HSS Shank Ø / insert size 0608/06 mm	260022 0608/06
Boring bar HSS Shank Ø / insert size 0810/06 mm	260022 0810/06
Boring bar HSS Shank Ø / insert size 1012/06 mm	260022 1012/06
Boring bar HSS Shank Ø / insert size 1216/06 mm	260022 1216/06

Set of insert screws Type 7

269028 7