

Garant

HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 0608/06mm


Order data

Order number	260023 0608/06
GTIN	4045197652102
Item class	21T

Technical description

Pack of insert screws	269028 7
Insert size	6 mm
ISO code toolholder	AH0608H SCLCR/L06
Head length L ₁	25 mm
Centre offset L ₃	4 mm
Neck width L ₄	6 mm
suitable indexable insert	CC.. 0602..
Minimum pre-drill Ø D _{min}	8 mm
Overall length L	100 mm
Clamping height L ₂	7 mm
Setting angle κ	95 degrees
Shank Ø D _s	8 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8