

**Garant**
**HSS boring bar AH.. SCLCL, for indexable inserts CC., left-hand**

**Order data**

Order number	260025
GTIN	4045197652218
Item class	29W

**Technical description**

ISO code toolholder	AH1012K SCLCR/L06
ISO code toolholder	AH0608H SCLCR/L06
ISO code toolholder	AH0810J SCLCR/L06
ISO code toolholder	AH1216M SCLCR/L06
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Clamping height L <sub>2</sub>	7 mm
Clamping height L <sub>2</sub>	9 mm
Clamping height L <sub>2</sub>	11 mm
Clamping height L <sub>2</sub>	15 mm
Minimum pre-drill Ø D <sub>min</sub>	8 mm
Minimum pre-drill Ø D <sub>min</sub>	12 mm
Minimum pre-drill Ø D <sub>min</sub>	14 mm
Minimum pre-drill Ø D <sub>min</sub>	18 mm

Centre offset L <sub>3</sub>	4 mm
Centre offset L <sub>3</sub>	6 mm
Centre offset L <sub>3</sub>	7 mm
Centre offset L <sub>3</sub>	9 mm
Neck width L <sub>4</sub>	6 mm
Neck width L <sub>4</sub>	8 mm
Neck width L <sub>4</sub>	10 mm
Neck width L <sub>4</sub>	12 mm
Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
Overall length L	150 mm
Overhang L <sub>1</sub>	50 mm
Overhang L <sub>1</sub>	38 mm
Overhang L <sub>1</sub>	32 mm
Overhang L <sub>1</sub>	25 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes
Type of product	Boring bar

## Accessories

Boring bar HSS Shank Ø / insert size 0608/06 mm	260023 0608/06
Boring bar HSS Shank Ø / insert size 0810/06 mm	260023 0810/06
Boring bar HSS Shank Ø / insert size 1012/06 mm	260023 1012/06
Boring bar HSS Shank Ø / insert size 1216/06 mm	260023 1216/06

Set of insert screws Type 7

269028 7