

Garant

**Carbide boring bar E.. SCLCL 95°, for indexable inserts CC.., left-hand, Shank
Ø / insert size: 20/09mm**



Order data

Order number	260017 20/09
GTIN	4045197651921
Item class	21T

Technical description

Head length L_1	16 mm
Pack of insert screws	269028 8
Insert size	9 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	E20S SCLCR/L09
Centre offset L_3	12 mm
Minimum pre-drill $\varnothing D_{min}$	23 mm
Overall length L	250 mm
Clamping height L_2	19 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15