

Garant

HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 0810/06mm

**Order data**

Order number	260023 0810/06
GTIN	4045197652126
Item class	21T

Technical description

Head length L_1	32 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{\min}$	12 mm
ISO code toolholder	AH0810J SCLCR/L06
Centre offset L_3	6 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Neck width L_4	8 mm
Overall length L	110 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8