

Garant
Clamping toolholder SCLCL 95°, for indexable inserts CC., left-hand, Shank / insert size: 25/12mm

Order data

Order number	260007 25/12
GTIN	4045197651761
Item class	21T

Technical description

ISO code toolholder	SCLCR/L 2525M12
Insert size	12 mm
Shim	269005 6
Pack of insert screws	269028 20
Functional width L ₄	32 mm
suitable indexable insert	CC.. 1204..
Shank size	25 mm
Shim screw	269013 5
Head length L ₁	20 mm
Overall length L	150 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 6	269005 6
Shim screw Type 5	269013 5
Set of insert screws Type 20	269028 20
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15