

Garant

HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 1012/06mm


Order data

| | |
|--------------|----------------|
| Order number | 260023 1012/06 |
| GTIN | 4045197652140 |
| Item class | 21T |

Technical description

| | |
|--|-------------------|
| Centre offset L_3 | 7 mm |
| ISO code toolholder | AH1012K SCLCR/L06 |
| Insert size | 6 mm |
| Pack of insert screws | 269028 7 |
| Neck width L_4 | 10 mm |
| Minimum pre-drill $\varnothing D_{\min}$ | 14 mm |
| suitable indexable insert | CC.. 0602.. |
| Head length L_1 | 38 mm |
| Overall length L | 125 mm |
| Clamping height L_2 | 11 mm |
| Setting angle κ | 95 degrees |
| Shank $\varnothing D_s$ | 12 mm |
| Standard | Works standard |
| Application type | left-hand |
| Boring depth up to | 5×D |
| Tool material | HSS |

| | |
|-----------------|-------------------------------|
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

| | |
|--|------------|
| Set of insert screws Type 7 | 269028 7 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |