

**Garant**

**Clamping toolholder SCLCL 95°, for indexable inserts CC., left-hand, Shank / insert size: 8/06mm**



### Order data

Order number	260007 8/06
GTIN	4045197651686
Item class	21T

### Technical description

suitable indexable insert	CC.. 0602..
Shank size	8 mm
Pack of insert screws	269028 22
ISO code toolholder	SCLCR/L 0808D06
Insert size	6 mm
Functional width L <sub>4</sub>	10 mm
Head length L <sub>1</sub>	9 mm
Overall length L	60 mm
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Set of insert screws Type 22

269028 22