

**Garant**

**HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 12/06mm**


**Order data**

Order number	260023 12/06
GTIN	4045197652157
Item class	21T

**Technical description**

Overhang $L_1$	60 mm
Pack of insert screws	269028 7
Insert size	6 mm
Centre offset $L_3$	7 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	AH12M SCLCR/L06
Minimum pre-drill $\varnothing D_{min}$	14 mm
Overall length L	150 mm
Clamping height $L_2$	11 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8