

Garant

HSS boring bar AH.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 16/09mm


Order data

Order number	260022 16/09
GTIN	4045197652058
Item class	21T

Technical description

Insert size	9 mm
Pack of insert screws	269028 8
ISO code toolholder	AH16Q SCLCR/L09
Centre offset L_3	11 mm
Overhang L_1	80 mm
suitable indexable insert	CC.. 09T3..
Minimum pre-drill $\varnothing D_{\min}$	18 mm
Overall length L	180 mm
Clamping height L_2	15 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15