

Garant

HSS boring bar AH.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 0410/03mm


Order data

Order number	260022 0410/03
GTIN	4045197651969
Item class	21T

Technical description

Head length L_1	24 mm
suitable indexable insert	CC.. 0301..
Centre offset L_3	2.5 mm
Neck width L_4	4 mm
Insert size	3 mm
Minimum pre-drill $\varnothing D_{\min}$	5 mm
Pack of insert screws	269028 13
ISO code toolholder	AH0410H SCLCR/L03
Overall length L	100 mm
Clamping height L_2	9 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 13	269028 13
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6