

**Garant**

**HSS boring bar AH.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 1216/06mm**


**Order data**

Order number	260023 1216/06
GTIN	4045197652164
Item class	21T

**Technical description**

ISO code toolholder	AH1216M SCLCR/L06
Centre offset $L_3$	9 mm
suitable indexable insert	CC.. 0602..
Insert size	6 mm
Neck width $L_4$	12 mm
Head length $L_1$	50 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	18 mm
Overall length $L$	150 mm
Clamping height $L_2$	15 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8