



Boring bar set, steel, with IC, right-hand, Type: SET06



Order data

Order number	260036 SET06
GTIN	4045197656629
Item class	29W

Description

Supplied with:

Plastic case

Technical description

ISO code toolholder	A0810J SCLCR/L06
ISO code toolholder	A1216M SCLCR/L06
ISO code toolholder	A0608H SCLCR/L06
ISO code toolholder	A1012K SCLCR/L06
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Head length L ₁	22 mm
Head length L ₁	27 mm
Head length L ₁	33 mm

Head length L_1	42 mm
Minimum pre-drill $\varnothing D_{\min}$	8 mm
Minimum pre-drill $\varnothing D_{\min}$	11 mm
Minimum pre-drill $\varnothing D_{\min}$	13 mm
Minimum pre-drill $\varnothing D_{\min}$	17 mm
Clamping height L_2	7 mm
Clamping height L_2	9 mm
Clamping height L_2	11 mm
Clamping height L_2	15 mm
Centre offset L_3	4 mm
Centre offset L_3	6 mm
Centre offset L_3	7 mm
Centre offset L_3	9 mm
Overall length L	100 mm
Overall length L	110 mm
Overall length L	125 mm
Overall length L	150 mm
Neck width L_4	6 mm
Neck width L_4	8 mm
Neck width L_4	10 mm
Neck width L_4	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar

Accessories

Boring bar steel Shank Ø / insert size 0608/06 mm	260032 0608/06
Boring bar steel Shank Ø / insert size 0810/06 mm	260032 0810/06
Boring bar steel Shank Ø / insert size 1012/06 mm	260032 1012/06
Boring bar steel Shank Ø / insert size 1216/06 mm	260032 1216/06
Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8