

Garant

Steel boring bar A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 8/06mm


Order data

| | |
|--------------|---------------|
| Order number | 260033 8/06 |
| GTIN | 4045197652300 |
| Item class | 21T |

Technical description

| | |
|---|-------------------------------|
| Centre offset L_3 | 6 mm |
| Insert size | 6 mm |
| suitable indexable insert | CC.. 0602.. |
| Pack of insert screws | 269028 7 |
| ISO code toolholder | A08H SCLCR/L06 |
| Minimum pre-drill $\varnothing D_{min}$ | 10 mm |
| Overall length L | 100 mm |
| Clamping height L_2 | 7 mm |
| Setting angle κ | 95 degrees |
| Shank $\varnothing D_s$ | 8 mm |
| Standard | DIN 8024 |
| Application type | left-hand |
| Boring depth up to | 3×D |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8