

**Garant**

**Steel boring bar A.. PDUNL 93°, for indexable inserts DN., left-hand, Shank Ø / insert size: 20/11mm**


**Order data**

Order number	250627 20/11
GTIN	4045197650627
Item class	21T

**Technical description**

Lever	259015 10
ISO code toolholder	A20Q PDUNR/L11
Centre offset $L_3$	16 mm
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	DN.. 1104..
Lever screw	259018 12
Overall length L	180 mm
Clamping height $L_2$	19 mm
Setting angle $\kappa$	93 degrees
Shank $\varnothing D_s$	20 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

---

**Accessories**

Lever Type 10	259015 10
Lever screw Type 12	259018 12