



## Boring bar set, steel, with IC, right-hand, Type: SET09



### Order data

Order number	260036 SET09
GTIN	4045197657701
Item class	29W

### Description

#### Supplied with:

Plastic case

### Technical description

suitable indexable insert	CC.. 09T3..
Pack of insert screws	269028 8
ISO code toolholder	A16Q SCLCR/L09
ISO code toolholder	A25R SCLCR/L09
ISO code toolholder	A20R SCLCR/L09
Minimum pre-drill $\varnothing D_{min}$	20 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
Minimum pre-drill $\varnothing D_{min}$	28 mm
Clamping height $L_2$	15 mm
Clamping height $L_2$	18 mm

Clamping height L <sub>2</sub>	23 mm
Centre offset L <sub>3</sub>	10.7 mm
Centre offset L <sub>3</sub>	10.5 mm
Centre offset L <sub>3</sub>	14.5 mm
Overall length L	180 mm
Overall length L	200 mm
Overall length L	200 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Type of product	Boring bar

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659906 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15
Boring bar steel Shank Ø / insert size 20/09 mm	260032 20/09
Boring bar steel Shank Ø / insert size 16/09 mm	260032 16/09
Boring bar steel Shank Ø / insert size 25/12 mm	260032 25/12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500