

**Garant**

**Steel boring bar A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 12/06mm**


**Order data**

Order number	260033 12/06
GTIN	4045197652324
Item class	21T

**Technical description**

Centre offset $L_3$	9 mm
suitable indexable insert	CC.. 0602..
ISO code toolholder	A12L SCLCR/L06
Pack of insert screws	269028 22
Insert size	6 mm
Minimum pre-drill $\varnothing D_{min}$	16 mm
Overall length L	140 mm
Clamping height $L_2$	11 mm
Setting angle $\kappa$	95 degrees
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8