

Garant
**Clamping toolholder PDJNR 93°, for indexable inserts DN., right-hand,
Shank / insert size: 16/11 mm**

Order data

Order number	250610 16/11
GTIN	4045197650481
Item class	21T

Technical description

Shim pins pack	259044 4
Shim punches pack	259047 3
ISO code toolholder	PDJNR/L 1616H11
Lever screw	259018 6
Head length L ₁	25 mm
suitable indexable insert	DN.. 1104..
Shank size	16 mm
Lever	259015 7
Insert size	11 mm
Shim	259031 7
Functional width L ₄	20 mm
Overall length L	100 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 7	259015 7
Lever screw Type 6	259018 6
Shim Type 7	259031 7
Set of shim pins 10 pieces Type 4	259044 4
Shim punches set 10 pieces Type 3	259047 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5