

Garant

Steel boring bar A.. SCLCL 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 12/06mm


Order data

| | |
|--------------|---------------|
| Order number | 260032 12/06 |
| GTIN | 4045197652249 |
| Item class | 21T |

Technical description

| | |
|-------------------------------|-------------------------------|
| ISO code toolholder | A12L SCLCR/L06 |
| Minimum pre-drill Ø D_{min} | 16 mm |
| Pack of insert screws | 269028 22 |
| Centre offset L_3 | 9 mm |
| Insert size | 6 mm |
| suitable indexable insert | CC.. 0602.. |
| Overall length L | 140 mm |
| Clamping height L_2 | 11 mm |
| Setting angle κ | 95 degrees |
| Shank Ø D_s | 12 mm |
| Standard | Works standard |
| Application type | right-hand |
| Boring depth up to | 3×D |
| Through-coolant | yes |
| Application | Internal longitudinal turning |
| Type of product | Boring Bar |

Accessories

| | |
|--|------------|
| Set of insert screws Type 22 | 269028 22 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8 | 674248 TX8 |