

**Garant**

**Clamping toolholder PDJNR 93°, for indexable inserts DN., right-hand,  
Shank / insert size: 25/11 mm**



## Order data

Order number	250610 25/11
GTIN	4045197650504
Item class	21T

## Technical description

Shim pins pack	259044 4
Shim punches pack	259047 3
Lever	259015 7
suitable indexable insert	DN.. 1104..
ISO code toolholder	PDJNR/L 2525M11
Shim	259031 7
Insert size	11 mm
Shank size	25 mm
Head length L <sub>1</sub>	33 mm
Functional width L <sub>4</sub>	32 mm
Lever screw	259018 6
Overall length L	150 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle $\kappa$	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 7	259015 7
Lever screw Type 6	259018 6
Shim Type 7	259031 7
Set of shim pins 10 pieces Type 4	259044 4
Shim punches set 10 pieces Type 3	259047 3
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
Precision Bit for hexagon, 1/4 inch E 6.3 Hexagon 2,5 mm	674242 2,5