

Garant
HSS boring bar AH.. SCLDL, for indexable inserts CDCT, left-hand, Overhang / insert size: 50/S4mm

Order data

Order number	268706 50/S4
GTIN	4045197591968
Item class	21V

Technical description

ISO code toolholder	AH06X SCLDR/LS4
Insert size	4 mm
Centre offset L_3	3.5 mm
Minimum pre-drill $\varnothing D_{min}$	6.92 mm
Pack of insert screws	269028 10
suitable indexable insert	CDCT S4010.
Overall length L	75 mm
Clamping height L_2	5.54 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 10	269028 10
Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm	659957 200
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6