

Garant**MicroClamp drill chuck plain, L = 100, Type: 0,2-3****Order data**

Order number	302407 0,2-3
GTIN	4045197556837
Item class	31H

Description**Version:**

- For clockwise and anticlockwise rotation.
- Concentricity ≤ 0.005 mm.
- Transmissible torque 7 Nm.
- Maximum speed 60,000 rpm.
- Operated from the side.
- Permissible tightening torque 2 Nm.
- Clamping range 0.2 – 3.4 mm.

Supplied with:

Clamping wrench with T-handle size 2.

Technical description

$\varnothing D_2$	12 mm
Clamping range $\varnothing D_1$	0.2 - 3.4 mm
Shank $\varnothing d$	16 mm
External $\varnothing D$	19 mm
Shank tolerance	h6
Balance quality G at rotational speed	G 2.5 at 18,000 rpm
Machining strategy	HSC
Type of product	Micro drill chuck

