

Garant

**HSS boring bar AH.. STLDR 95°, for indexable inserts TDAT, right-hand,
Overhang / insert size: 50/07mm**


Order data

Order number	268812 50/07
GTIN	4045197591982
Item class	21V

Technical description

Pack of insert screws	269028 12
Centre offset L_3	3.71 mm
suitable indexable insert	TDAT 07010.
Insert size	7 mm
Minimum pre-drill $\varnothing D_{min}$	7.06 mm
ISO code toolholder	AH06X STLDR/L07
Overall length L	75 mm
Clamping height L_2	5.54 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	5xD
Tool material	HSS
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 12	269028 12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6