

**Garant**

**HSS boring bar AH.. STLDR 95°, for indexable inserts TDAT, right-hand,  
Overhang / insert size: 66/07mm**



## Order data

|              |               |
|--------------|---------------|
| Order number | 268812 66/07  |
| GTIN         | 4045197591999 |
| Item class   | 21V           |

## Technical description

|                                          |                               |
|------------------------------------------|-------------------------------|
| suitable indexable insert                | TDAT 07010.                   |
| Centre offset $L_3$                      | 4.8 mm                        |
| ISO code toolholder                      | AH08H STLDR/L07               |
| Pack of insert screws                    | 269028 12                     |
| Insert size                              | 7 mm                          |
| Minimum pre-drill $\varnothing D_{\min}$ | 9.14 mm                       |
| Overall length L                         | 100 mm                        |
| Clamping height $L_2$                    | 7.49 mm                       |
| Setting angle $\kappa$                   | 95 degrees                    |
| Shank $\varnothing D_s$                  | 8 mm                          |
| Standard                                 | Works standard                |
| Application type                         | right-hand                    |
| Boring depth up to                       | 5×D                           |
| Tool material                            | HSS                           |
| Through-coolant                          | yes                           |
| Application                              | Internal longitudinal turning |

Type of product

Boring Bar

---

**Accessories**

Set of insert screws Type 12

269028 12

Torque screwdriver with scale, to take interchangeable  
blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6

674248 TX6