

Garant

**Carbide boring bar E.. STLDR 95°, for indexable inserts TDAT, right-hand,
Overhang / insert size: 75/07mm**



Order data

Order number	268822 75/07
GTIN	4045197562647
Item class	21V

Technical description

Pack of insert screws	269028 12
suitable indexable insert	TDAT 07010.
Insert size	7 mm
Centre offset L_3	3.71 mm
ISO code toolholder	E06J STLDR/L07
Minimum pre-drill $\varnothing D_{min}$	7.06 mm
Overall length L	110 mm
Clamping height L_2	5.54 mm
Setting angle κ	95 degrees
Shank $\varnothing D_s$	6 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD
Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 12	269028 12
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX6	674248 TX6