

Garant

HSS boring bar AH.. STFCL 90°, for indexable inserts TC.., left-hand, Shank Ø / insert size: 20/11 mm



Order data

Order number	260923 20/11
GTIN	4045197653505
Item class	21T

Technical description

Centre offset L_3	13 mm
suitable indexable insert	TC.. 1102..
Head length L_1	32 mm
Pack of insert screws	269028 7
Minimum pre-drill $\varnothing D_{min}$	23 mm
ISO code toolholder	AH20R STFCL/L11
Insert size	11 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8