

Garant

Carbide boring bar E.. STFCR 90°, for indexable inserts TC.., right-hand, Shank Ø / insert size: 16/11mm



Order data

Order number	260918 16/11
GTIN	4045197653383
Item class	21T

Technical description

ISO code toolholder	E16R STFCR/L11
Minimum pre-drill Ø D _{min}	19 mm
Pack of insert screws	269028 7
suitable indexable insert	TC.. 1102..
Insert size	11 mm
Head length L ₁	25 mm
Centre offset L ₃	10 mm
Overall length L	200 mm
Clamping height L ₂	15.4 mm
Setting angle κ	90 degrees
Shank Ø D _s	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D
Tool material	Carbide
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8