

Garant

HSS boring bar AH.. STFCL 90°, for indexable inserts TC., left-hand, Shank Ø / insert size: 10/11mm


Order data

Order number	260923 10/11
GTIN	4045197653475
Item class	21T

Technical description

Insert size	11 mm
Centre offset L_3	7 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Head length L_1	16 mm
suitable indexable insert	TC.. 1102..
ISO code toolholder	AH10K STFCL/L11
Pack of insert screws	269028 7
Overall length L	125 mm
Clamping height L_2	9 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8