

Garant

HSS boring bar AH.. STFCL 90°, for indexable inserts TC.., left-hand, Shank Ø / insert size: 12/11mm



Order data

Order number	260923 12/11
GTIN	4045197653482
Item class	21T

Technical description

Centre offset L_3	9 mm
Head length L_1	20 mm
Pack of insert screws	269028 7
ISO code toolholder	AH12M STFCL/L11
suitable indexable insert	TC.. 1102..
Minimum pre-drill Ø D_{min}	14 mm
Insert size	11 mm
Overall length L	150 mm
Clamping height L_2	11 mm
Setting angle κ	90 degrees
Shank Ø D_s	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	5×D
Tool material	HSS
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8