

Garant

Steel boring bar A.. STLCL 90°, for indexable inserts TC.., left-hand, Shank Ø / insert size: 20/16mm


Order data

Order number	260935 20/16
GTIN	4045197653611
Item class	21T

Technical description

Minimum pre-drill $\varnothing D_{\min}$	25 mm
suitable indexable insert	TC.. 16T3..
Centre offset L_3	13 mm
Head length L_1	36.6 mm
ISO code toolholder	A20R STFCL/L16
Pack of insert screws	269028 8
Insert size	16 mm
Overall length L	200 mm
Clamping height L_2	18 mm
Setting angle κ	90 degrees
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product	Boring Bar
-----------------	------------

Accessories

Set of insert screws Type 8	269028 8
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15