

Garant

Steel boring bar A.. STFCR 90°, for indexable inserts TC.., right-hand, Shank Ø / insert size: 12/11mm


Order data

Order number	260934 12/11
GTIN	4045197653536
Item class	21T

Technical description

Minimum pre-drill Ø D _{min}	16 mm
Head length L ₁	26.5 mm
Pack of insert screws	269028 7
Insert size	11 mm
Centre offset L ₃	9 mm
ISO code toolholder	A12L STFCR/L11
suitable indexable insert	TC.. 1102..
Overall length L	140 mm
Clamping height L ₂	11 mm
Setting angle κ	90 degrees
Shank Ø D _s	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar

Accessories

Set of insert screws Type 7

269028 7

Torque screwdriver with scale, to take interchangeable
blades maximum torque 500 cNm

659957 500

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8

674248 TX8